Adapter to OGN, OGN-SMD

Fuse Carriage with Handle for OGN, OGN-SMD





2.5W/10A





Description

- Better access to fuse-links on PCB's

- Printed circuit boards with tightly packed components. Colour coding allows for quick and safe replacement of fuses.

References

Mating adapter to OGN; OGN-SMD

Weblinks

pdf-datasheet, html-datasheet, General Product Information, Approvals, CE declaration of conformity, RoHS, CHINA-RoHS, REACH, e-Shop, SCHURTER-Stock-Check, Distributor-Stock-Check, Detailed request for product


Technical Data

Fuse-Link	5 x 20 mm
Rated Power Acceptance IEC	2.5W / 10A @ Ta 23°C
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cover	Thermoplastic black / white UL 94V-0
Storage Conditions	0°C to 60°C, max. 70% r.h.


Contact Resistance < m Ω at 20 mV

Dimension









Packaging Unit

Bulk (100 pcs.)

Fuses