

Data sheet

Commercial Art.No.: 70.320.0628.0

Bottom BAS GUT GK 6 A

revos BASIC size 6 open-bottom base single locking lever

1011011010001010010101101
 0100110110010110100101010
 101001101100111001010010
**DIGITALIZATION
 IN PROGRESS**
 101010011010101010101010
 1101010011011001011010010
 1010101010010101101010011

Commercial Art.No.	70.320.0628.0
EAN	4015573220027
Order Unit	1

Certificates / Approvals



Technical data

General

Housing material	Aluminium
Color	Grey
Surface	With powder coating
Degree of protection (IP)	IP65
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

Model

Construction	6
Model	Equipment mounted (feed-through)
Locking mechanism	Single locking lever
Cable entry	None
Type of cable	None
With cable screw gland	No
Thread size PG	
Hinged lid	No
EMC-version	No
Length	80 mm
Width	43.5 mm
Height	28.9 mm

Classification

ECLASS 8.1	27440202
ETIM 7.0	EC000437
ETIM 6.0	EC000437
ETIM 5.0	EC000437

ETIM 4.0	EC000437
ETIM 3.0	EC000437