

Alnico Cylindrical Bar Magnet datasheet

- Alnico 5 magnet material
- Magnetically stable at high temperatures
- Max. operating temperature 220°C
- Mild steel pot, aluminium spacer.
- Zinc plated body
- Diameter ground to H6 tolerance
- Custom designs available
- Sold in pairs



Product Information

Product No.	Diameter	Length*	Weight / pair	Gauss
	<i>mm</i>		<i>kg</i>	
E805	6	20	0.008	1200
E806	8	25	0.018	1200
E807	10	30	0.035	1200

*magnetic axis