

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640068**
Status: **Active**
Overview: Perma-Seal Terminals
Description: Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9)

Documents:

3D Model [Product Specification PS-19902-011-001 \(PDF\)](#)
3D Model (PDF) [Product Specification PS-19902-013-001 \(PDF\)](#)
Drawing (PDF) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19164
 Crimp Quality Equipment Yes
 Overview Perma-Seal Terminals
 Product Name Perma-Seal
 Type Ring
 UPC 800753113527

Physical

Barrel Type Closed
 Insulation NiAc
 Material - Plating Mating Tin
 Net Weight 2.449/g
 Packaging Type Bag
 Stud Size 3/8" (M9)
 Wire Insulation Diameter 7.87mm
 Wire Size AWG 10, 12
 Wire Size mm² 3.09-5.01

Material Info

Engineering Number SC-240-38

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19164-041



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade Hand	640017400
Crimp Tool	
Power Crimp Tool	640057400
Head for Terminals	
10-22 AWG Wire	
ServiceGrade Hand	640160041
Crimp Tool - Ratchet	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19164-0068](#)