



Sample photo

Order symbol: ABS 17/16-3
Product nbr: 7585165
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056771
EI. number:
 Finland: 3438242
 Electric No. 8212016745
 Denmark:
 Electric No. Sweden: 7585165

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	166	160	134	FP 17/16 Front plate (aluminium)
inch:	6.5	6.3	5.3	FC PC 17/16 Frame of PC front plate
Materials:	Rating:			
Material: ABS	Ingress Protection (EN 60529): IP65			
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07			
Cover colour: Smoked grey	Electrical insulation: Totally insulated			
Gasket material: EPDM & PUR	Halogen free (DIN/VDE 0472, Part 815): 1			
Temperatures:	Flammability Rating: UL 94 HB			
Temperature °C (short term): -40 ... 80 °C	Glow Wire Test (IEC 695-2-1) °C: 650			
Temperature °C (continuous): -40 ... 60 °C	NEMA Class: NEMA 1, 3, 3R, 12, 13			
Temperature °F (short term): -40 ... 175 °F				
Temperature °F (continuous): -40 ... 140 °F				
Accessories:				
MP 17/16	Mounting plate			

