




1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	A
1	2	3	4	5	6	7	B
1	2	3	4	5	6	7	C
1	2	3	4	5	6	7	D
1	2	3	4	5	6	7	E
1	2	3	4	5	6	7	F
1	2	3	4	5	6	7	G
1	2	3	4	5	6	7	H



PLUG TYPE



Hank Dimension



Wire cross section

WSW P/N	L(mm)
AK500/16-OE-5-0.5	500±20
AK500/16-OE-5-1	1000±50
AK500/16-OE-5-1.5	1500±50
AK500/16-OE-5-2	2000±50
AK500/16-OE-5-3	3000±50

- NOTES:**
- Material:**
- 1.SJT 3x16AWG(1.31MM<sup>2</sup>) VW-1 Shielded,60°C 300V.
  - 2.Jacket Color: Black.
  - 3.E-Green, L-Black, N-White.
- Electrical Test:**
- 1.100% Open & Short Testing.
  - 2.Insulation Resistance: 100MΩ(Min).
  - 3.Voltage: 500V DC/1Min.

**RoHS compliant**  
Unit: mm

Scale	FREE																		
TOLERANCE																			
DIM	TOL	①	Update conductor spec	09.04.2015	Joanna	Drawn	01.04.2015	Joanna	Approved	01.11.2018	Amy	ASSMANN WSW-No.	AK500/16-OE-5-X	Customer-No.	ASSMANN WSW-No.	AK500/16-OE-5-X	Drawing-No.	ASS 7359 CA	rev02
Angle	TOL	②	Update	01.11.2018	Segal	Drawn	01.04.2015	Joanna	Approved	01.11.2018	Amy	ASSMANN WSW-No.	AK500/16-OE-5-X	Customer-No.	ASSMANN WSW-No.	AK500/16-OE-5-X	Drawing-No.	ASS 7359 CA	rev02
		③	Drawn	01.04.2015	Joanna	Drawn	01.04.2015	Joanna	Approved	01.11.2018	Amy	ASSMANN WSW-No.	AK500/16-OE-5-X	Customer-No.	ASSMANN WSW-No.	AK500/16-OE-5-X	Drawing-No.	ASS 7359 CA	rev02
			Modification																

