



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2501-02A	2.50	7.50
A2501-03A	5.00	10.00
A2501-04A	7.50	12.50
A2501-05A	10.00	15.00
A2501-06A	12.50	17.50
A2501-07A	15.00	20.00
A2501-08A	17.50	22.50
A2501-09A	20.00	25.00
A2501-10A	22.50	27.50
A2501-11A	25.00	30.00
A2501-12A	27.50	32.50
A2501-20A	47.50	52.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01	料号 PART NO.	A2501-NA	版本 REV.	A
			X.±0.25	X'±2°	审核 CHECK	张名 2013、07、03	品名 TJ3直针		页次 SHEET	1/1
			.X±0.20	.X'±1°	核准 APPROVAL	张名 2013、07、05	客户料号 CUTM. NO.	深圳市金航标电子有限公司	www.kinghelm.com.cn	
			.XX±0.15	.XX'±0.5°	单位 UNITS	MM	比例 SCALE	1:1	KH-2501GW-05A-Z	
			.XXX±0.10	.XXX'±0.5°					0755-28190160	