

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552209019](#)

Status: **Active**

Overview:

Description: Flamar Distribution Box Cable, WSOR Jacket, Unshielded, 19 Circuits, 3x(0.75mm²) with Green-Yellow Ground + 16x(0.34mm²) / 3x(19 AWG) with Green-Yellow Ground + 16x(22 AWG), 10.20mm (.402") Diameter, 100.0m (328.08') Length, Black

Agency Certification

UL E172949

General

Product Family Cable
Series [155220](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview flamar_standard_industrial_cables
Product Name Flamar, Signal and Control
UPC 889056463478

Physical

Bending Radius - Minimum > 10xOD
Cable Length 100.0m
Circuits (Loaded) 19 (3+16)
Color - Cable Jacket Black
Insulation TPE
Material - Outer Jacket WSOR
Net Weight 0.151/kg
Outer Jacket Diameter 10.20mm
Packaging Type Reel
Temperature Range - Operating -25° to +80°C
Wire Size AWG 19, 22
Wire Size mm² 0.34, 0.75
Wire/Cable Type UL AWM 21215 / CSA

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 600V

Material Info

Engineering Number B80-19-1X100M

Reference - Drawing Numbers

Product Specification 1552209001-P1E

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155220](#) Series

Use With

Brad M23 [120230](#) , [120233](#)