

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 plug EM 24VAC/DC BU/GN/YE/RD



| | |
|-----------|------------|
| Part No.: | 698.250.75 |
| Series: | Kompakt 37 |



| MECHANICAL DATA | |
|-----------------------------|--------------------------------|
| Height | 209 mm |
| Diameter | 38 mm |
| Materials | PC |
| Dome colour | Blue Green Red Yellow |
| Housing colour | Black |
| Protection category | IP65 |
| Connection | M12 plug 8-pole |
| Cable entry | Membrane grommet |
| Cable entry minimum | d = 1 mm |
| Cable entry maximum | d = 9 mm |
| Tension relief | Pull-out protection |
| Type of fixing | Built-in mounting |
| Working temperature minimum | -20°C |
| Working temperature maximum | +50°C |
| UL Type Rating | Type 12 Type 4X |
| Weight with packaging | 154 g |
| Product weight | 100 g |

| ELECTRICAL DATA | |
|-----------------------------|--------------------------------|
| Operating voltage | 24V |
| Operating voltage type | AC/DC |
| Operating voltage frequency | 50Hz |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 24 VDC |
| Rated operational current | 135 mA |
| Rated inrush current | 500 mA |
| Protection class | Protection class 2 |
| Pollution degree | 3 In the connection area: 2 |

| OPTICAL DATA | |
|--------------|--------------------------------|
| Light source | LED |
| Light colour | Blue Green Red Yellow |




For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Completely pre-assembled Signal Towers / KOMPAKT 37
K37 plug EM 24VAC/DC BU/GN/YE/RD

| | |
|----------------------|------------------|
| Optical signal image | Permanent |
| Service life optical | 50,000 h maximum |

DRAWING



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.