

# EGG.0K.305.CLL

### **SUMMARY**

#### # Wires

Low voltage

5



Image is for illustrative purpose only

Series	ОК		
Termination type	Female solder		
IP rating	68		
AWG wire size	30.00 - 22.00		
Cable Ø	1.00 - 5.00 mm		
Status	active		
Matching parts	FGG.0K.305.CLAC50		

Download <u>Request a quote</u> <u>Eplan</u> <u>Catalog</u>

## **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model	EG*: Fixed receptacle, nut fixing
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Weight	11.80 g

#### Performance

Configuration	OK.305 : 5 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	6.5 Amps

#### **Specifications**

Contact Type: Solder Contact Dia.: 0.7 mm (0.028in) Bucket Dia.: 0.8 mm (0.031in) Max. Solid Conductor: 0.34 mm^2 (AWG 22) Max. Stranded Conductor: 0.34 mm^2 (AWG 22) R (max): 6.1 mOhm Vtest (contact-shell): 700 V (AC), 990 V (DC) Vtest (contact-contact): 1000 V (AC), 1400 V (DC)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

#### Others

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +200°C Humidity (max): <=95% [at 60 deg C /140 F] Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz) Salt Spray Corrosion: >1000 hr

### DRAWINGS

Draws





0°



#### Dimensions

	А	В	E	L	м	N	S1	\$3	e
mm.	18	19.5	6	21.7	4	20.1	12.5	17	M14x1.0
in.	0,71	0,77	0,24	0,85	0,16	0,79	0,49	0,67	

### **RECOMMENDED BY LEMO**

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

PVC	GREY			
PVC	Black			
TPR (medical)	Grey	€		
PVC	GREY			
	Grey	>€		
		▶€		
	Grey	>€		
PVC	Black			
		▶€		
PVC	Black			
PVC	Black			
PVC	Grey			
PVC	Grey			
	PVC TPR (medical) PVC PVC PVC PVC PVC PVC PVC PVC	PVCBlackTPR (medical)GreyPVCGREYGreyGreyPVCGreyPVCBlackPVCBlackPVCBlackPVCBlackPVCBlackPVCBlackPVCBlackPVCBlackPVCBlack		

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO: EGG.0K.305.CLL