

Specification Sheet

Part Number: 157-00083



Design gives quick and easy assembly by hand without the need for tools.

Mount can be used in a wide variety of applications where 5mm weld studs or 5mm ISO bolts.

Design provides low insertion force and high extraction force.

Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg

Article Number 157-00083

Type T50SSBS6OT-E

Color Black (BK)

Quantity Per bag

Product Description The Standoff Stud Mount tie applies easily to weld studs and secures bundles away from fixing holes. These are used primarily in the automotive industry, but can be used in a variety of applications.

Short Description Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg

Global Part Name T50SSBS6OT-E-PA66HS-BK

Minimum Tensile Strength (Imperial)	45.0
Minimum Tensile Strength (Metric)	200
Length L (Imperial)	6.0
Length L (Metric)	160
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.4
Bundle Diameter Max (Metric)	35.0
Stud Diameter (Metric)	6.0 mm
Stud Diameter (Imperial)	0.24

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988