

Technical Datasheet

tasker® T35 – 4x11 AWG

FirestoP®

Flexible Loudspeaker Cable

✓RoHS₃



A

B

C

CATEGORY

Flexible Speaker Cable (See News Brochure)

APPLICATIONS

Professional Loudspeakers and premade cables

- A:** Black Soft **Flame Retardant PVC** Sheath.
Outer cable Diam. Ø 12,00 (±0,20) mm.
- B:** Core Insulation with **PVC** Sheath. Diam. Ø 3,70 (±0,20) mm.
Color Code: Red, Black, Blue and Green.
- C:** O.F.C. red copper formation 82x0,25 mm.
Nom. Cross section 4x11 AWG.

MARKING

tasker® T35 4x11 AWG O.F.C. Loudspeaker Cable - FirestoP® - Made In Italy

CUSTOM

This product may be custom produced also in **L.S.Z.H.** polymer, **PE**, **PUR**, with or without Metallic Armor.

PRODUCTION

Cable Properties

Conductor Resistance	4,31 Ω/Km
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS3 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Restricted Mobile	Mobile Limitata	Informazioni	X	Ver. B / 16.05.19
		Outdoor	Esterno			Mobile	Mobile			
		Outdoor Direct Burial	Esterno Interrato			Mobile in Drag Chain	Mobile in Catena			