

TERMINAL BLOCK Connector

KLSelectronic
www.cnkls.com

PCB Series

KLS2-128IH-5.00/5.08 Series Pitch=5.00mm/5.08mm

Electrical :


Rated voltage: 300V
Rated current: 10A
Contact resistance: 20mΩ
Insulation resistance: 5000MΩ/1000V
Withstanding Voltage: AC2000V/1Min
Wire range: 24-12AWG 2.5mm²

Material

Screws: M2.5 steel Zinc plated
Contact: Brass, Ni plated
Pin header: Brass, Tin plated
Housing: PA66, UL94V-0

Mechanical

Temp. Range: -40°C~+105°C
MAX Soldering: +250°C for 5 Sec.
Torque: 0.4Nm (3.6 lb.in)
Strip length: 6-7mm



ORDER INFORMATION

Product NO.: KLS2-128IH-5.00-XXP X X X

Pos. NO.

Series No.

Pitch: 5.00=5.00mm 5.08=5.08mm
10.00=10.00mm 10.16=10.16mm

Number of Pole

Customer Request

Screw: C=Cross Screw
S=Slot Screw

Color: 1=Gray 2=Blue 3=Black
4=Green 5=Orange 6=Red
7=Transparent 8=Yellow 9=White

All specification & dimensions are subject to change, please call your nearest KLS sales representative for update information