

3=Black

## Screwless Series

KLS2-142V-5.08 Series Pitch=5.08mm

#### **Electrical:**

Rated voltage: 300V Rated current: 10A Contact resistance:  $20m\Omega$ 

Insulation resistance:  $5000M\Omega/1000V$  Withstanding Voltage: AC1500V/1Min Wire range:  $22\text{-}14AWG\ 1.5MM^2$ 


#### **Material**


Pin header: Brass, Tin plated Housing: PA66, UL94V-0 Wire guard: Stainless steel

### Mechanical

Temp. Range: -40°C~+105°C MAX Soldering: +250°C for 5 Sec.

Strip length: 10mm





# ORDER INFORMATION

Product NO.: KLS2-142V-5.08-XXP X X

Pos. No.

Series No.

Pitch: 5.08=5.08mm

Number of Pole

Customer Request

Color: 1=Gray
4=Green 5=Orange
7=Transparent 8=Yellow