# **TERMINAL BLOCK Connector**

## **PCB** Series

### KLS2-300-5.00 Series Pitch=5.00mm/10.00mm

#### **Electrical:**


Rated Voltage: 300V Rated Current: 16A Contact Resistance: 20mΩ Insulation Resistance: 5000MΩ/1000V Withstanding Voltage: AC1500V/1Min Wire Range: 22-14AWG 2.5mm<sup>2</sup>

#### **Material**

Screws: M3 steel Zinc plated Wire guard: phosphor bronze Ni plated or stainless steel Pin header: Brass, Tin plated Housing: PBT,UL94V-0

#### **Mechanical**

Temp. Range: -30°C~+120°C MAX Soldering: ++250°C for 5 Sec. Torque: 0.5Nm (4.5lb.in) Strip length: 4.5-5mm



All specification & dimensions are subject to change, please call your nearest KLS sales representative for update information

