TERMINAL BLOCK Connector

PCB Series

KLS2-305V-5.00 Series Pitch=5.00mm/10.00mm

Electrical:


Rated voltage: 300VRated current: 10AContact resistance: $20m\Omega$ Insulation resistance: $5000M\Omega/1000V$ Withstanding Voltage: AC1500V/1Min Wire range: 22-14AWG 2.5mm²

Material

Screws: M2.5 steel Zinc plated Wire guard: phosphor bronze Ni plated or stainless steel Pin header: Brass, Tin plated Housing: PBT,UL94V-0

Mechanical

Temp. Range: -30°C~+120°C MAX Soldering: +250°C for 5 Sec. Torque: 0.4Nm (3.6lb.in) Strip length: 4.5-5mm



All specification & dimensions are subject to change, please call your nearest KLS sales represesntative for update information

