

PCB Series

KLS2-340-3.81 Series Pitch=3.81mm

Electrical:

Rated voltage: 250V Rated current: 10A Contact resistance: $20m\Omega$ Insulation resistance: $5000M\Omega/1000V$ Withstanding Voltage: AC1500V/1Min Wire range: 24-18AWG, $1.0mm^2$

Material


Screws: M2 steel Zinc plated Wire guard: phosphor bronze Ni plated Pin header: Brass, Tin plated


Housing: PBT Mechanical

Temp. Range: -40°C~+105°C MAX Soldering: 250°C for 5 Sec.

Torque: 0.2Nm Strip length: 5-6mm







ORDER INFORMATION

Product No.: KLS2-340-3.81-XXP-X X

Pos. No.

Series No.

Pitch: 3.81=3.81mm

Number of Pole

Screw: C=Cross Screw
S=Slot Screw
Color: 1=Gray
4=Green
7=Transparent
8=Yellow
9=White