

## Specification Sheet

Part Number: T40I0M4

Engineered and manufactured for maximum performance and quality. Made from 100% high-quality plastic to ensure efficient recycling.

Inside serration for a strong grip onto bundles.

Easy application either manually or with a tensioning tool.

Bent tail allows for simpler insertion.



Cable Tie, 11" Long, UL Rated, 40lb Tensile Strength, PA66, Black, 1000/pkg

**Article Number** 111-04604

**Type** T40I

**Color** Black (BK)

**Quantity Per** bag

**Product Description** T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description** Cable Tie, 11" Long, UL Rated, 40lb Tensile Strength, PA66, Black, 1000/pkg

**Global Part Name** T40I-PA66-BK

**Minimum Tensile Strength (Imperial)** 40.0

**Minimum Tensile Strength (Metric)** 180.0

**Length L (Imperial)** 11.0

**Length L (Metric)** 295.0

**Identification Plate Position** none

**Releasable Closure** No

**Variant** Inside Serrated

**Width W (Imperial)** 0.16

**Width W (Metric)** 4.0

**Bundle Diameter Min (Imperial)** 0.06

**Bundle Diameter Min (Metric)** 1.5

**Bundle Diameter Max (Imperial)** 3.15

**Bundle Diameter Max (Metric)** 80.0

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V-2
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988