

Specification Sheet

Part Number: 151-00927



Pre-drilled holes allows for easy installation by hand.

Cable can be removed and reinstalled without removing the clip, providing multiple use options.

Made of PA66HIRHSUV material for withstanding extreme conditions.

Fir Tree C-Clip, .24"-.30" Bundle Dia, .03"-.25" Panel, .26" Mnt Hole, PA66HIRHSUV, Black, 100/pkg

Article Number 151-00927

Type SC6.6

Color Black (BK)

Quantity Per bag

Product Description The C Clip with fir tree mount is ideal for panels with pre-drilled holes. Easy installation by hand eliminates the need for any tools. Once installed, the cable simply snaps into the clip. The cable can be removed and reinstalled without removing the clip. Made from PA66HIRHSUV material, the clip offers increased flexibility along with heat resistance and UV stability.

Short Description Fir Tree C-Clip, .24"-.30" Bundle Dia, .03"-.25" Panel, .26" Mnt Hole, PA66HIRHSUV, Black, 100/pkg

Global Part Name

SC6.6-PA66HIRHSUV-BK

Width W (Imperial)

0.72

Width W (Metric)

18.26

Bundle Diameter Min (Imperial)

0.24

Bundle Diameter Min (Metric)

6.0

Bundle Diameter Max (Imperial)

0.29

Bundle Diameter Max (Metric)

7.6

Height H (Imperial)

1.32

Height H (Metric)

33.43

Panel Thickness Min (Imperial)

0.03

Panel Thickness Max (Imperial)

0.25

Panel Thickness Min (Metric)

0.7

Panel Thickness Max (Metric)

6.35

Mounting Hole Diameter D (Imperial)

0.26

Mounting Hole Diameter D (Metric)

6.6 mm

Mounting Hole Diameter D Max (Metric)

6.6

Disc Diameter (Metric)	18.55
Disc Diameter (Imperial)	0.73
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

