

# electrical connection box

## VAVE-L1-1VK7-LP

Part number: 573942

★ Core product range

FESTO



### Data sheet

Feature	Value
Assembly position	Any
Cable attribute	For static applications
Polarity protected	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V 24 V
Surge strength	0.8 kV
Degree of contamination	3
Corrosion resistance classification CRC	0 - No corrosion stress
Protection class	IP65
Ambient temperature	-5 ... 60 °C
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	20 g
Electrical connection	Angled socket / cable Square design/open end 2-pin / 2-wire
Cable structure	2x0,25
Cable diameter	3.4 mm
Cable diameter tolerance	± 0,2 mm
Cable length	1 m
Protective earth connection	Not available
Mounting type	On solenoid valve with self-tapping screw
Housing colour	Black
Materials note	Conforms to RoHS
Material housing	PA
Material cable sheath	TPV