



Выключатель-разъединитель, низкое напряжение, 160 А, AC 690 V, NH00, AC22B, 3P, IEC



Powering Business Worldwide™

№ для зак. **EBV0033TV1**
Каталог № **EBV0033TV1**

Программа поставок

Программа поставок			Принадлежности к предохранителю
Основная функция			Выключатель-разъединитель
Область применения			низкое напряжение
Номинальный ток	I	A	160
Номинальное напряжение			AC 690 V
Типоразмер			NH00
Категория применения			AC22B
Описание			185 mm busbar mounting Одновременное 3-фазное переключение V-образные зажимы
Защита			IP20
Количество полюсов			3P
возможно использование для типоразмеров/оборудования			Предохранители NH00
Стандарт/сертификат			IEC
Форма			вертикально
Стандарты/предписания			IEC 60947-1 IEC 60947-3

Технические характеристики согласно ETIM 6.0

Low-voltage industrial components (EG000017) / In-line fuse base (EC001046)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse strip (ecl@ss8.1-27-37-14-02 [AKF059010])			
Model			Fuse switch disconnecter
Double interrupting			No
Rated permanent current I _u		A	160
Distance between rail centre, 40 mm			No
Distance between rail centre, 50 mm			No
Distance between rail centre, 60 mm			No
Distance between rail centre, 100 mm			No
Distance between rail centre, 185 mm			Yes
Max. rated operation voltage U _e AC		V	690
Conditioned rated short-circuit current I _q		kA	80
Type of electrical connection of main circuit			Cable clamp
Number of poles			3
Construction size fuse insert			NH00