



**Выключатель-разъединитель, низкое напряжение, 160 А, AC 690 V, NH00, AC22B, 3P, IEC**



Powering Business Worldwide™

№ для зак. **EBV0033SV1**  
Каталог № **EBV0033SV1**

### Программа поставок

Программа поставок			Принадлежности к предохранителю
Основная функция			Выключатель-разъединитель
Область применения			низкое напряжение
Номинальный ток	I	A	160
Номинальное напряжение			AC 690 V
Типоразмер			NH00
Категория применения			AC22B
Описание			185 mm busbar mounting однофазное переключение V-образные зажимы
Защита			IP20
Количество полюсов			3P
возможно использование для типоразмеров/оборудования			Предохранители NH00
Стандарт/сертификат			IEC
Форма			вертикально
Стандарты/предписания			IEC 60947-1 IEC 60947-3

### Технические характеристики согласно ETIM 6.0

Low-voltage industrial components (EG000017) / In-line fuse base (EC001046)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse strip (ecl@ss8.1-27-37-14-02 [AKF059010])			
Model			Fuse switch disconnector
Double interrupting			No
Rated permanent current Iu		A	160
Distance between rail centre, 40 mm			No
Distance between rail centre, 50 mm			No
Distance between rail centre, 60 mm			No
Distance between rail centre, 100 mm			No
Distance between rail centre, 185 mm			Yes
Max. rated operation voltage Ue AC		V	690
Conditioned rated short-circuit current Iq		kA	80
Type of electrical connection of main circuit			Cable clamp
Number of poles			3
Construction size fuse insert			NH00