

LogiLink®




4K HDMI™ Switch, 2x2 Ports 4K/60 Hz, Downscaler

Art. No.: HD0039

This high performance 4K HDMI Switch can switch any of two HDMI sources to two HDMI displays simultaneously; resolution up to 4K@60 Hz and is HDCP 2.2 compliant. Featuring 4K to 1080p downscale function.

Features:

- » Allows 2 HDMI sources to be display on 2 HDMI displays at the same time
- » Resolution up to UHD 4K@60 Hz (YUV 4:4:4) and Full 3D
- » Bandwidth up to 18 Gbps (6 Gbps at 600 MHz per channel)
- » Supports HDCP 2.2, DDC, HDR and CEC functions
- » Supports 36 bit Deep Color (12 bit per channel)
- » Supports downscaler to downscale the input 4K resolution to 1080p by the FHD displays
- » Supports switching input source EDID with 1.4/2.0
- » Supports selection of high or low audio modes
- » Supports LPCM 7.1, Dolby TrueHD and DTS-HD Master Audio™
- » Perfect solution for home, school, bars and restaurants



- (a) Auto mode LED indicator
- (b) HDMI output 1-2 ports LED indicator
- (c) HDMI input 1-2 ports LED indicator
- (d) Input source EDID mode switch
- (e) Audio High/Low mode select button (cyclic switch)
- (f) Input port select button (cyclic switch), and long press 5 seconds to turn off the product
- (g) DC 5 V input
- (h) HDMI input 1-2 ports
- (i) HDMI output 1-2 ports





*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



HD0039



Made in China



Specifications:

Input Ports	2x HDMI-A female
Output Ports	2x HDMI-A female
HDMI Version	2.0
HDCP Version	2.2
CEC (Consumer Electronics Control)	Yes
HDR (High-Dynamic Range)	Yes
Output Resolution	480i@60 Hz, 576i@50 Hz, 1080i@50/60 Hz, 480p@60 Hz, 576p@50 Hz, 720p@50/60 Hz, 1080p@24/25/30/50/60 Hz, 4K@24/25/30 Hz, 4K@50/60 Hz 4:4:4
Video Bandwidth	Up to 18 Gbps
3D Supporting	Yes
Input and output DDC signal	Yes
TMDS (Transition Minimized Differential Signaling)	Yes
LED Indication	Yes
Color Depth	6 bit, 8 bit, 10 bit and 12 bit
8 Bit/10 Bit Encoding	Yes
Chassis Material	Metal
Power By	5 V/1 A (5 W max.)
Uncompressed Audio	LPCM 7.1
Compressed Audio	DTS-HD Master Audio™, Dolby TrueHD
Operating Temperature	0–70°C
Operating Humidity	10–85% RH (no condensation)
Dimensions	11.6 x 5.2 x 2.3 cm
Weight	158 g
Color	Black



*The specifications and pictures are subject to change without prior notice.
 *All trade names referenced are the registered trademarks of their respective owners.



HD0039



4 052792 062373

Made in China

Specification of External Power Supply:

Input Voltage	100–240 V, 50/60 Hz 0.2 A max.
Output Power	5 V/1 A, 5 W
DC Plug	5.5 x 2.1 mm
Dimensions	51 x 36 x 59 mm
Cable Length	1.2 m
Weight	0.07 kg



Package Contents:

- » 1x HDMI Switch
- » 1x Power Adapter
- » 1x User Manual

Package Information:

- » Packing Dimension: 193 x 145 x 60 mm
- » Packing Weight: 0.35 kg
- » Carton Dimension: 505 x 235 x 340 mm
- » Carton Q'ty: 15 pcs
- » Carton Weight: 5.8 kg



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.



HD0039



4 052792 062373

Made in China