

# S/FTP Cat. 6A LSZH patch cord, grey, 30 m

PP6A-LSZHCU-30M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts



## Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A
- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

## Packaging

Q'ty in crtn, pcs	10
Crtn volume, CUM	0.046
Crtn weight, kgs	18.46
Individual package size LxWxH:	180x310x40 mm
Carton size LxWxH:	400x290x400 mm
Country of origin	CN
Barcode	8716309111966
Customs code	8544421000

## Specifications

Patch cord category 6A SSTP (shielded)  
 Length: according to the item  
 Structure: AWG 27 (7 x 0.135 mm wire), COPPER  
 FM-PE insulation of the wire: 1.0 mm  
 With LDPE filler  
 With polyester tape  
 With aluminum foil  
 Drain hose: not used  
 With Braid : 16 x 4/0.12mm  
 Outer insulation: 5.8 mm  
 Color: according to the item  
 Operation up to 250 MHz

## Certificates

