



WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
49	AWG 30	49
50	AWG 30	50

Part Number	Revision	Cable length ( L )
3315 243 050 0015	01	500 ± 5
3315 243 020 0014	01	200 ± 3
3315 243 010 0013	01	100 ± 3
3315 243 005 0013	00	50 ± 3
3315 243 080 0080	00	800 ± 10
3315 243 030 0080	00	300 ± 5
3315 243 012 0080	00	120 ± 3
3315 243 040 0080	00	400 ± 5

C1  
HAR-FLEX 50P FEMALE CONNECTOR  
WITH STRAIN RELIEF

C2  
HAR-FLEX 50P FEMALE CONNECTOR  
WITH STRAIN RELIEF

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE  
HARTING P/N

	All rights reserved Department HCS - CN HARTING Customised Solutions D-32339 Espelkamp	Created by ZHENGL Zheng	Inspected by WANG Wang	Standardisation CHENJU Chen	Date 2018-06-06	State Final Release	Doc-Key / ECM-Nr. 100621839/UGD/000/F 500000135979
All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
Title Har-flex 50Pole,Dul-end,With SR,L=XX MM						Rev. F	
Type TB						Number 33150005	
Page 1/1						Page 1/1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33152430200014](#) [33152430500015](#) [33152430100013](#)