

Rittal – The System.

Faster – better – everywhere.

Cable gland, brass – SZ 2411.871

Date : Apr 26, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Cable gland, brass – SZ 2411.871

created: 26.04.2021 build on www.rittal.com/uk-en



Product description

Benefits: Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.
Clamping membranes for even tightening and strain relief to protect the cables

Material: Brass
Seal: TPE/NBR

Surface finish: Nickel-plated

**Protection category
IP to IEC 60 529:** IP 68 (5 bar, 30 min)

Product description

Dimensions: Height: 54 mm

Thread: Type: M63 x 1.5

Thread length: 14 mm

Min. cable diameter: 34 mm

Max. cable diameter: 44 mm

**Operating
temperature:** Operation (environment): -40 °C...+100 °C

Width across flats: 64 mm

Packs of: 1 pc(s).

Weight/pack:	0.52 kg
Copper weight (kg per piece):	0
EAN:	4028177810020
Customs tariff number:	73269098
ETIM 7.0:	EC000441
ETIM 6.0:	EC000441
eCl@ss 8.0/8.1:	27149109
eCl@ss 6.0/6.1:	27149109
Product description:	SZ Cable gland, brass, size: M63x1,5, for cables ø 34-44 mm
Approvals	
Approvals:	UL + C-UL VDE
Certificates:	NA
Declarations:	Declaration of conformity