

## Tripp Lite Waber Industrial Power Strip, 4-Outlet, 6 ft. (1.83 m) Cord, 5-15P, Lighted On/Off Switch

MODEL NUMBER: 4SPDX



### Highlights

- 4 outlets
- 7.38 in. length
- Lighted master switch
- All-metal housing

### Package Includes

- 4SPDX Power Strip
- Warranty information
- Instruction manual

### Description

The Waber-by-Tripp Lite 4SPDX Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 4 NEMA 5-15R output receptacles with 1.20-in. center-to-center spacing, 6-ft. (1.83 m) AC line cord and keyhole mounting in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 4SPDX ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 4 NEMA 5-15R  
ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)  
FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 4 NEMA 5-15R output receptacles with 1.20-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. (1.83 m) AC line cord

## Specifications

OVERVIEW	
UPC Code	037332108197
INPUT	

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
Outlet Spacing	1.20 in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted combination switch / circuit breaker
<b>PHYSICAL</b>	
Color	Beige
Material of Construction	Metal
Power Cord Color	Beige
Housing Color	Beige
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	127mm
Outlets Measurement (Center to Center)	1.18 in.
Receptacle Color	Beige
Shipping Dimensions (hwd / in.)	9.50 x 2.00 x 5.50
Shipping Dimensions (hwd / cm)	24.13 x 5.08 x 13.97
Shipping Weight (lbs.)	1.40
Shipping Weight (kg)	0.64
Unit Dimensions (hwd / in.)	1.500 x 7.500 x 2.500

# TRIPP-LITE

by **EATON**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Unit Dimensions (hwd / cm)	19.1 x 6.4 x 3.8
Outlet Spacing	1.20 in.
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EATON**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.