



PANEL CUT-OUT

Rating :

15A 250V AC T105 UL cUL  
10A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength:  $\geq 80N$

Operating Life:  $\geq 5000$  cycles

Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min  
terminals to Base:3750V AC (50-60Hz)1min

Leakage Current : 1mA

Insulation Resistance:  $\geq 100M\Omega$  500V DC

Body Materil: PBT 94V-2-0

A4				普通公差	深圳市华灿天禄电子有限公司							
A3				COMMON TOLERANCE :								
A2				UP TO 5	$\pm 0.20$	单位	mm	投影	品名 PRODUCT NAME	Ac Inlet C14型	比例 SCALE	Free
A1				ABOVE 5 TO 30	$\pm 0.30$	绘图	吴瑜	核影				
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	$\pm 5^\circ$	日期	2013.07.16	核准	型号 MODEL NO.	DB-14		
						日期		核准	料号 PART NO.	DB-14-13P		