



DATASHEET

RIGID TOGGLE TOGGLE LATCH 40032 ZI



DESCRIPTION:

This Design is particularly recommended for equipment liable to vibration.
A spring catch fitted to the inside wall locks the toggle arm down making accidental release difficult.
A wedged blade such as a small screw driver should be used to open the spring safety lock.

Suitable for screw fixing using 4 x M5 screws.
Holes provided for tamper sealing
Normal latch to catch fixing center is 94mm
Maximum operating tension: 250 daN

Supplied with dimensions template for marking out and catch.

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 90 x 40 x 22 mm
- Depth: 22 mm
- Length: 90 mm
- Width: 40 mm

