

PCB Terminal Blocks

Item Number: 256-401
Marking: MODULAR TERMINAL BLOCK 2 SOLDER PINS/POLE
Colour: grey

Product Image



Technical Data

Wiring:	front-entry		
Number of Clamping Units:	1	Number of Clamping Units:	1
Minimum Cross Section [mm ²]:	0.08	max. conductor cross section [mm ²]:	2.5
Minimum Cross Section [AWG]:	28	max. conductor cross section [AWG]:	14
Pin spacing [mm]:	5	Pin spacing [inch]:	0.197
Pin spacing 2 [mm]:	5.08	Pin spacing 2 [inch]:	0.2
rated voltage EN [V]:	250	rated voltage UL [V]:	300
rated voltage CSA [V]:	300	Test Voltage:	
rated search voltage [kV]:	4	Current (Amps.) UL [A]:	15
Current (Amps.) EN [A]:	16	Test Current [A]:	
Current (Amps.) CSA [A]:	15	Stripped Length [inch]:	0.22
Stripped Length [mm]:	5-6		
Pollution Degree:	3		