





BOOMELE



孔位	2	3	4	5	6	7	8	9	10	11
A	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	25.40
B	5.74	8.28	10.82	13.36	15.90	18.44	20.98	23.52	26.06	28.60
孔位	12	13	14	15	16	17	18	19	20	
A	27.94	30.48	33.02	35.56	38.10	40.64	43.18	45.72	48.26	
B	31.44	33.98	36.52	39.06	41.60	44.14	46.68	49.22	51.76	



UNIT: MM	TYPE: CONNECTOR	MODEL NO: 2510-Y	日期 DATE YR/MO/DAY	2008/06/20	页次 1 OF 1 PAGE 1 OF 1					
			公差 TOLERANCE	± 0.15	角度公差 ANGLES	± 1.5°	比例 SCALE	FIT	版本 VER	1.0
设计控制 DESIGNER BY	SUNDIXIONG	文件编号 DOCUMENT NUMBER								
绘制 DRAFTSMAN BY	WUZHENG FANG									
审核 CHECKED BY	LIMING MAO	供应商 COME OUT WITH								
批准 APPROVED BY	LIUXUPING	BOOMELE								
			BOOM 乐清市博穆电子有限公司 BOOM ELECTRONIC CO., LTD. YUEQING							