


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

4-40thread(UNC)


4X THUMBSCREW



Amphenol Cables on Demand




2X 4-40 Hex Nut




D-SUB
15PIN Male

D-SUB
15PIN Female


LENGTH



Drain Wire Soldered



JACKET ALU/MY



360° Copper Shield

Drain Wire Soldered

LENGTH & P/N Table

LENGTH	P/N	Cable Color
(18") ±.5FT ±.1 inch	CS-DSDHD15MF0-001.5	GREY
2.5FT ±.1 inch	CS-DSDHD15MF0-002.5	GREY
5FT ±.2 inch	CS-DSDHD15MF0-005	GREY
7.5FT ±.2 inch	CS-DSDHD15MF0-007.5	GREY
10FT ±.3 inch	CS-DSDHD15MF0-010	GREY
15FT ±.3 inch	CS-DSDHD15MF0-015	GREY
25FT ±.4 inch	CS-DSDHD15MF0-025	GREY

PIN OUT:


Male	Female	Color
PIN1	PIN1	Black
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN4	Orange
PIN5	PIN5	Yellow
PIN6	PIN6	Green
PIN7	PIN7	Blue
PIN8	PIN8	Purple
PIN9	PIN9	Gray
PIN10	PIN10	White
PIN11	PIN11	Pink
PIN12	PIN12	Light Green
PIN13	PIN13	Black/White
PIN14	PIN14	Brown/White
PIN15	PIN15	Red/White
SHIELD	SHIELD	Drain Wire



REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	07/02/2007	
A1	Add wiring color	13/JAN/2012	
A2	Add 18" Length	9/APR/2014	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	±.XX	ANGLES	±X°
X	±.XX		
XXX	±.XXX		



APPROVALS	DATE
LF	9/APR/2014
BA	9/APR/2014

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

**Deluxe Hingh Density
15PIN D-Sub MF**

SIZE	DWG. NO.	REV.
A	CS-DSDHD15MF0-XXX	A2

NOTES: UNLESS OTHERWISE SPECIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[CS-DSDHD15MF0-010](#) [CS-DSDHD15MF0-015](#) [CS-DSDHD15MF0-007.5](#) [CS-DSDHD15MF0-002.5](#) [CS-DSDHD15MF0-025](#) [CS-DSDHD15MF0-005](#)