

## ROLINE HQ VGA Cable with Ferrite, HD15 M - HD15 M 20 m



Supplier: ROLINE  
Article Number: 11.04.5270-2  
Pieces per Packing Unit: 2

**roline**  
Designed for Professionals

### Description

- High quality cable for connection of a monitor to a graphics card or VGA splitter or amplifier
- As monitor connection cable with two additional ferrite cores
- 3 coax lines for the RGB signals and 7 AWG28 wires
- Connector casings moulded
- Double screened cable (braided and foil shield)
- Hand locking screws

### Technical Data - Overview

Product group	Cable
Conveyance good	No
Length	20.0 m
side 1 connector	D-Sub HD 15 Male
side 2 connector	D-Sub HD 15 Male
Left Connector Type	HD D-Sub 15-pin (HD-15), VGA
Left Connector Gender	Male
Right Connector Type	HD D-Sub 15-pin (HD-15), VGA
Right Connector Gender	Male
Colour (Cable)	black
Area of application	External
Cable shielding	Double screened
Hand locking screws	Yes
Cable composition	3 Coax RGB 7xAWG28
Technical particularity	with ferrite

### Datasheet

We reserve the right to amend any or all information without prior notice. Furthermore, all prices and offers are subject to change. We assume no responsibility for misprints or the accuracy of technical information. Product pictures and/or graphics are of an exemplary nature and can deviate from the original.