



Main

Range	Resi9
Product name	Resi9 MP
Product or component type	Enclosure
Enclosure type	Modular enclosure
Number of 18 mm modules per row	8
Number of horizontal rows	1
Type of front cover	Translucid
Width	196 Mm outside:
Height	198 Mm outside:
Depth	101.5 Mm outside:

Complementary

Enclosure mounting	Surface
9 mm pitches	16
Total number of 18 mm modules	8
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Mounting plate description	Without mounting plate
Cable entry	1 trunking flange 1 bare flange
Terminal block function	Earth / neutral
Number of terminal blocks	1 earth (screwed) with 8 outgoing 1 neutral (screwed) with 8 outgoing
Distribution block outgoing	1 x 16 mm ² for earth 1 x 16 mm ² for neutral 3 x 6 mm ² for earth 3 x 6 mm ² for neutral 4 x 10 mm ² for earth 4 x 10 mm ² for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal depth	80 Mm
Colour	Front face: white (RAL 9003) Door: translucent
Market segment	Small commercial Residential

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality labels	IMQ
Fire resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.000 Cm
Package 1 Width	19.500 Cm
Package 1 Length	22.800 Cm
Package 1 Weight	636.000 G
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.000 Cm
Package 2 Width	40.000 Cm
Package 2 Length	60.000 Cm
Package 2 Weight	7.232 Kg
Unit Type of Package 3	P12
Number of Units in Package 3	160
Package 3 Height	120.000 Cm
Package 3 Width	80.000 Cm
Package 3 Length	120.000 Cm
Package 3 Weight	127.712 Kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**