


Mechanical Specifications

D	21.0 mm Max
T	6.0 mm Max
Lead Diameter	1.0 mm Nom
S	7.8 mm Nom
L	38.0 mm Min
Straight Leads	Standard



Electrical Specifications

Resistance @ 25°C	7.0 Ω ± 25%
Transition Temp	120 Deg C
Max voltage Rating	350 v rms
Switch Current @ 25°C	1.600A
Continuous Current @ 25°C	0.850A
Heat Capacity	2.0 Joules/°C
Dissipation Constant	22.50 mW/°C
Thermal Time Constant	65.0 seconds
Max Body Temperature @ Max voltage	172°C

Ametherm, Inc
961 Fairview Dr.
Carson City, NV 89701
Telephone: **800-808-2434**
Fax: 775 884-0670
www.Ametherm.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[CL20 7R0120](#) [CL20 7R0120-B](#) [CL20 7R0120-A](#)