

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Push-in thermocouples with compensating cable

- for temperatures from 0 to 600°C
- available with different thermocouples
- with stainless steel protection tube
- silicone compensating cable or with metal braiding
- also with 90° cable entry

Push-in thermocouples are preferred for measuring temperatures on solids, such as hot-plates and welding jaws. Applications include ovens, plant engineering and machinery.

Depending on the version, compensating cables are suitable for use in dry areas within the temperature range -20 to +350°C. The connection of the cable to the protection tube incorporates strain relief. A cable protector is available as an option.

Protection tubes in stainless steel protect the measuring insert from chemical influences and mechanical damage.

The measuring insert is fitted with thermocouples to EN 60 584 and DIN 43 710.



Technical data

Connection

available with cable ends as: bare wires, with ferrules, receptacle or multipole connector

Compensating cable

silicone, ambient temperature -50 to +180°C
metal braiding, ambient temperature -20 to +350°C
compensating cable available with shielding (option)

Protection tube

stainless steel 1.4571, 6mm dia.

Measuring insert

insulated assembly:
1 x Fe-Con L, DIN 43 710, Cl. 2, operating temperature -200 to +600°C
1 x NiCr-Ni K, EN 60 584, Cl. 2, operating temperature -200 to +600°C

Accessories

pocket, see Data Sheet 90.9721


Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk


885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com



Dimensions



Type 901105/10



Type 901105/20

Delivery address: Mackenrodtstraße 14,
36039 Fulda, Germany
Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
e-mail: mail@jumo.net
Internet: www.jumo.net

JUMO House
Temple Bank, Riverway
Harlow, Essex CM 20 2TT, UK
Phone: +44 1279 635533
Fax: +44 1279 635262
e-mail: sales@jumo.co.uk
Internet: www.jumo.co.uk

885 Fox Chase, Suite 103
Coatesville PA 19320, USA
Phone: 610-380-8002
1-800-554-JUMO
Fax: 610-380-8009
e-mail: info@JumoUSA.com
Internet: www.JumoUSA.com




Order details: Push-in thermocouples with compensating cable

(1) Basic version

901105/10 Push-in thermocouple with stainless steel protection tube

901105/20 Push-in thermocouple with stainless steel protection tube angled at 90°



(2) Operating temperature in °C / compensating cable

x	x	380	-50 to +200°C / silicone
x	x	390	-50 to +300°C / metal braiding
x	x	840	0 to 300°C / metal braiding
x	x	843	0 to 350°C / metal braiding
x	x	848	0 to 400°C / metal braiding
x	x	858	0 to 600°C / metal braiding

(3) Measuring insert

x	x	1042	1 x Fe-Con L
x	x	1043	1 x NiCr-Ni K

(4) Protection tube diameter D in mm

x	x	6	6mm
---	---	---	-----

(5) Fitting length EL in mm (40 ≤ EL ≤ 500 for Type 901105/10)

x	x	12	12mm
x	x	50	50mm
x	x	60	60mm
x	x	100	100mm
x	x	200	200mm
x	x	300	300mm
x	x	...	please specify in plain text (50mm steps)

(6) Compensating cable end

x	x	03	bare cable ends
x	x	11	ferrules to DIN 46 228 Part 4 (standard)
x	x	13	receptacle 6.3 to DIN 46 247
x	x	80	multipole connector (please specify type in plain text)

(7) Compensating cable length AL in mm (500 ≤ AL ≤ 500000)

x	x	2500	2500mm
x	x	...	please specify in plain text (500mm steps)

(8) Extra codes

x	x	000	no extra code
x	x	309	uninsulated assembly (thermocouple welded to tip)
x	x	315	cable protector: coil
x	x	316	cable protector: tube

Order code - - - - - - / ,...

Order example 901105/10 - 848 - 1042 - 6 - 100 - 11 - 2500 / 000¹

1. List extra codes in sequence, separated by commas.

Stock versions:

(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)	Sales No.
901105/10	- 848	- 1042	- 6	- 50	- 11	- 2500	/ 315	90/00055455
901105/10	- 858	- 1042	- 6	- 100	- 11	- 2500	/ 315	90/00065812
901105/20	- 840	- 1042	- 6	- 60	- 11	- 2500	/ 000	90/00055448