



Self-amalgamating Tapes – Electrical Insulation Mastic

HelaTape Power 650

Features and Benefits

- Self-amalgamating insulation compound for sealing and padding cable jackets up to 1 kV
- Easily moulded by hand to conform to irregular shapes even during low temperatures
- Permanently elastic and resistant to aging
- Perfect adhesion to metal and all types of cable insulations and jackets
- Provides excellent moisture sealing
- Resistant to salt water, ozone, oil and corrosive chemicals
- Recommended use with HelaTape Flex vinyl electrical tape for mechanical protection



HelaTape Power 650 self-amalgamating mastic is highly flexible.

MATERIAL	Isobutene-Isoprene-Rubber (butyl rubber) (IIR)
Operating Temperature	+90 °C
Intermittent Operating Temperature	+130 °C
Water Absorption	0.1 %
Volume Resistance	10 ¹⁵ Ω cm
Dielectric Strength	19.7 kV/mm



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER650	3.20	38.0	1.5 m	Black (BK)	711-10300

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.