



### Wire Harness Tape – Soft and Flexible Fleece Tape

#### HelaTape Protect 300



HelaTape Protect 300 provides high noise reduction and media resistance.

#### Features and benefits

- Soft Polyester Fleece harnessing tape
- High noise reduction and very high resistance against abrasion
- Synthetic rubber based adhesive offers good heat and media resistance
- High temperature stability from -40 °C to +105 °C
- Material is very flexible and tearable by hand
- Excellent ageing resistance and stable against rotting

<b>MATERIAL</b>	Polyester (PET)
<b>Operating Temperature</b>	-40 °C to +105 °C
<b>Adhesion to Steel</b>	2 N/10 mm
<b>Adhesion to Backing</b>	2 N/10 mm
<b>Elongation at break</b>	10 %
<b>Breaking Strength</b>	30 N/10 mm



### Wire Harness Tape – High Noise Reduction Tape

#### HelaTape Protect 1500



HelaTape Protect 1500 is extremely soft and offers very high noise reduction.

#### Features and benefits

- High quality Polyamide Velours harnessing tape
- Highest noise reduction and very high resistance against abrasion
- Acrylate based adhesive offers very good heat and media resistance
- High temperature stability from -40 °C to +130 °C
- Material is extremely soft and very flexible
- Excellent ageing resistance, stable against rotting

<b>MATERIAL</b>	Polyamide (PA)
<b>Operating Temperature</b>	-40 °C to +130 °C
<b>Adhesion to Steel</b>	2.5 N/10 mm
<b>Adhesion to Backing</b>	2 N/10 mm
<b>Elongation at break</b>	50 %
<b>Breaking Strength</b>	100 N/10 mm



#### HelaTape Protect 300

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HETAPE-PROTECT300	0.30	19.0	25.0 m	Black (BK)	712-10001

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.

#### HelaTape Protect 1500

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HETAPE-PROTECT1500	1.50	25.0	4.0 m	Black (BK)	712-10000

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.