

## Han 3HPR-HBM-SL, powder coating



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 703 0311
Specification	Han 3HPR-HBM-SL, powder coating
HARTING eCatalogue	<a href="https://b2b.harting.com/09407030311">https://b2b.harting.com/09407030311</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> HPR
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight

### Version

Locking type	Screw locking
Size	3 A
Field of application	Hoods/housings for harsh outdoor environments
Pack contents	With seal screw

### Technical characteristics

Tightening torque (screw locking)	2 Nm
Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance

## Material properties

Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
CE	Yes

## Commercial data

Packaging size	1
Net weight	52 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09407030311](#)