



Neon Lamp Specification



型號 Type No.	尺寸 Dimensions (mm)		引出線 Wire size		起輝電壓 Breakdown (Max.)		電流 Current (mA)	串聯電阻值 Series resistance (KΩ)		壽命 Life (hrs)
	直徑 ØD +0.1/-0.3mm	長度 L +0.5/-1.5mm	線徑 mm ±0.02	線長 mm ±1	VAC	VDC		110-120 VAC	220-250 VAC	
標準亮度 Standard Brightness										
NE-2 3x10	3 ±0.2	10 +0/-1.5	0.35	30	65	90	0.3	150	330	25,000
NE-2 4x10	4	10 +0/-1.5	0.35	30	65	90	0.3	150	330	25,000
NE-2 4x10.5	4	10 +0.5/-1	0.35	30	65	90	0.3	150	330	25,000
NE-2 5x12	5	12 +0.5/-1	0.40	30	65	90	0.3	150	330	25,000
NE-2 5x13	5	13 +0/-2	0.40	30	65	90	0.3	150	330	25,000
NE-2 5x16	5	16 +0/-1.5	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x12	6	12 +0.5/-1	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x13	6	13 +0/-2	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x14	6	14	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x16	6	16	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x18	6	18	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x20	6	20	0.40	30	65	90	0.3	150	330	25,000
NE-2 6x22	6	22	0.40	30	65	90	0.3	150	330	25,000
准高亮度 Medium Brightness										
NE-2C 3x10	3 +/-0.2	10 +0/-1.5	0.35	30	65	90	0.5	100	320	25,000
NE-2C 4x10	4	10 +0/-1.5	0.35	30	65	90	0.7	68	220	25,000
NE-2C 4x10.5	4	10 +0.5/-1	0.35	30	65	90	0.7	68	220	25,000
NE-2C 5x12	5	12 +0.5/-1	0.40	30	65	90	1.0	47	150	25,000
NE-2C 5x13	5	13 +0/-2	0.40	30	65	90	1.0	47	150	25,000
NE-2C 5x16	5	16	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x12	6	12 +0.5/-1	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x13	6	13 +0/-2	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x14	6	14	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x16	6	16	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x18	6	18	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x20	6	20	0.40	30	65	90	1.0	47	150	25,000
NE-2C 6x22	6	22	0.40	30	65	90	1.0	47	150	25,000
高亮度 High Brightness										
NE-2H 3x10	3 +/-0.2	10 +0/-1.5	0.40	30	95	135	0.6	68	220	25,000
NE-2H 4x10	4	10 +0.5/-1	0.40	30	95	135	0.9	47	150	25,000
NE-2H 4x10.5	4	10 +0.5/-1	0.40	30	95	135	0.9	47	150	25,000
NE-2H 5x12	5	12 +0.5/-1	0.40	30	95	135	1.2	33	100	25,000
NE-2H 5x13	5	13 +0/-2	0.40	30	95	135	1.2	33	100	25,000
NE-2H 5x16	5	16	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x12	6	12	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x13	6	13 +0/-2	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x14	6	14	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x16	6	16	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x18	6	18	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x20	6	20	0.40	30	95	135	1.2	33	100	25,000
NE-2H 6x22	6	22	0.40	30	95	135	1.2	33	100	25,000

Neon Lamp Specification



型號 Type No.	尺寸 Dimensions (mm)		引出線 Wire size		起輝電壓 Breakdown (Max.)		電流 Current (mA)	串聯電阻值 Series resistance (KΩ)		壽命 Life (hrs)
	直徑 ØD +0.1/-0.3mm	長度 L +0.5/-1.5mm	線徑 mm ±0.02	線長 mm ±1	VAC	VDC		110-120 VAC	220-250 VAC	
超高亮度 Ultra-high Brightness										
NE-2UH 4x10	4	10 +0/-1.5	0.35	30	95	135	3.0	15	47	15,000
NE-2UH 5x12	5	12 +0.5/-1	0.40	30	95	135	4.0	12	37	15,000
NE-2UH 6x12	6	12 +0.5/-1	0.40	30	95	135	4.0	12	39	15,000
NE-2UH 6x16	6	16	0.40	30	95	135	4.0	12	39	15,000
NE-2UH 6x18	6	18	0.40	30	95	135	4.0	12	39	15,000
NE-2UH 6x20	6	20	0.40	30	95	135	4.0	12	39	15,000
綠燈 Green Lamp										
NE-2G 3x10	3 ±0.2	10 +0/-1.5	0.35	30	80	105	0.9	47	180	20,000
NE-2G 4x10	4	10 +0/-1.5	0.35	30	80	105	0.9	47	180	20,000
NE-2G 5x12	5	12 +0.5/-1	0.40	30	80	105	0.9	47	150	20,000
NE-2G 5x13	5	13 +0/-2	0.40	30	80	105	0.9	47	150	20,000
NE-2G 5x16	5	16	0.40	30	80	105	1.2	33	100	20,000
NE-2G 6x12	6	12 +0.5/-1	0.40	30	80	105	0.9	47	150	20,000
NE-2G 6x14	6	14	0.40	30	80	105	1.2	33	100	20,000
NE-2G 6x16	6	16	0.40	30	80	105	1.2	33	100	20,000
NE-2G 6x18	6	18	0.40	30	80	105	1.2	33	100	20,000
NE-2G 6x20	6	20	0.40	30	80	105	1.2	33	100	20,000
藍燈 Blue Lamp										
NE-2B 3x10	3 ±0.2	10 +0/-1.5	0.35	30	80	105	0.9	47	180	10,000
NE-2B 4x10	4	10 +0/-1.5	0.35	30	80	105	0.9	47	180	10,000
NE-2B 5x13	5	13 +0/-2	0.40	30	80	105	0.9	47	150	10,000
NE-2B 6x12	6	12 +0.5/-1	0.40	30	80	105	0.9	47	150	10,000
NE-2B 6x14	6	14	0.40	30	80	105	1.2	33	100	10,000
NE-2B 6x16	6	16	0.40	30	80	105	1.2	33	100	10,000
NE-2B 6x18	6	18	0.40	30	80	105	1.2	33	100	10,000
NE-2B 6x20	6	20	0.40	30	80	105	1.2	33	100	10,000

Specification subject to change without prior notice.