

Nibbler**GNA 2.0 Professional****The handy tool for cut-outs of all kinds**


- ▶ 500 watts of power
- ▶ Slim, narrow design for optimum handling
- ▶ Swivel-mounted die plate for better manoeuvrability in corners

Other features

- ▶ Easy-to-change cutting tools
- ▶ Lockable die plate for straight cuts
- ▶ Working to scribe mark and template easily possible
- ▶ For interior cut-outs



Technical data	
Order number	0 601 530 ...
Cutting track width	6 mm
Pre-drilling for interior cutout	16 mm
Smallest radius	3 mm
Steel up to 400 N/mm ²	2.0 mm
Steel up to 600 N/mm ²	1.4 mm
Steel up to 800 N/mm ²	1.0 mm
Scope of supply	
Allen key KW 2.5 (SP no. 1 907 950 003)	x
Die plate (2 608 639 900)	x
Punch (2 608 639 013)	x

500 W **2.0 kg****Nibbler****GNA 3.5 Professional****The most powerful model from Bosch**


- ▶ High-torque 620 W motor
- ▶ Particularly suitable for distortion-free cutting of alloyed steels and stainless steel plate
- ▶ Working to scribe mark and template easily possible

Other features

- ▶ Die plate holder can be set to metal plate thickness, enabling vibration-free work
- ▶ Long lifetime of punch and die plate leads to high cutting performance
- ▶ Die plate interchangeable; die can be sharpened
- ▶ Cut-off carbon brushes
- ▶ Good handling, also for left-handers



Technical data	
Order number	0 601 533 ...
Cutting track width	6 mm
Pre-drilling for interior cutout	41 mm
Smallest radius	70 mm
Steel up to 400 N/mm ²	3.5 mm
Steel up to 600 N/mm ²	2.4 mm
Steel up to 800 N/mm ²	1.6 mm
Scope of supply	
Allen key KW 4 (1 907 950 005)	x
Auxiliary handle (2 602 025 075)	x
Die plate (2 608 639 026)	x
Punch (2 608 639 025)	x
Supporting arm (2 607 001 190)	x

620 W **3.5 kg**

SP no. = Spare part number