

**MNX ABS 150/75 HG**



Sample photo

**Order symbol:** ABS 150/75 HG  
**Product nbr:** 6081314  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074022943  
**El. number:**  
 Finland 3420553  
 Denmark 8212023275  
 Italy 7361095  
 Sweden 2535754

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	L	W	H	Rating:
mm:	180	130	75	<b>Electrical insulation:</b> Totally insulated <b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes <b>Flammability Rating (UL 746 C 5):</b> UL 94 HB <b>Glow Wire Test (IEC 695-2-1) °C:</b> 650 <b>NEMA Class:</b> NEMA 1, 4, 4X, 6 <b>Ingress Protection (EN 60529):</b> IP 66/67 <b>Impact Resistance (EN 50102):</b> IK 07
inch:	7.1	5.1	3	

**Materials:**

<b>Material:</b>	ABS
<b>Gasket material:</b>	TPE
<b>Base colour:</b>	RAL 7035
<b>Cover colour:</b>	RAL 7035
<b>Cover screws material:</b>	Polyamide
<b>Cover screws colour:</b>	Grey

**Temperatures:**

<b>Short term:</b>	-40 ... 80 °C
<b>Continuous:</b>	-40 ... 60 °C
<b>Short term:</b>	-40 ... 175 °F
<b>Continuous:</b>	-40 ... 140 °F

**Accessories:**

MIV 150	Mounting plate (Galvanized steel)
MIN 10	DIN-15 Mounting rail
MIN 15	DIN-15 Mounting rail
MIV 10	DIN-35 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 150/180	Front plate (Aluminium)
HFP 180	Front plate hinge series (2 pcs)
FP 22046	Wall fastening lug (4 pcs)

**Certificates:**

Fimko
Europe EN 50298: 1998
Gost R

