



环保物料

TEL: 0769-82001899






SPECIFICATIONS

- 1.Voltage rating: 30V AC, DC
- 2.Current rating: 0.5A, AC, DC
- 3.Withstanding Voltage: 200V AC/minute
- 4.Insulation resistance:100M min
- 5.Temperature range: -25 ° C+85 ° C
- 6.Contact resistance: 20m max


HOUSING

Material: Nylon UL 94V0 or 94V2
 Standard color: White
 Contact : Phosphor Bronze or Brass
 Finish: Plated Tin or Plated Gold
 Mates with M0800VS, M0800RS series headers
 Poles:02-24P
 Part No.: M0800HI-xx-GN


Pin位数



CKT.	Dim A	Dim B	Dim C	Dim D
2	0.80	1.78	2.40	3.20
3	1.60	2.58	3.20	4.00
4	2.40	3.38	4.00	4.80
5	3.20	4.18	4.80	5.60
6	4.00	4.98	5.60	6.40
7	4.80	5.78	6.40	7.20
8	5.60	6.58	7.20	8.00
9	6.40	7.38	8.00	8.80
10	7.20	8.18	8.80	9.60
11	8.00	8.98	9.60	10.40
12	8.80	9.78	10.40	11.20
13	9.60	10.58	11.20	12.00
14	10.40	11.38	12.00	12.80
15	11.20	12.18	12.80	13.60
16	12.00	12.98	13.60	14.40
17	12.80	13.78	14.40	15.20
18	13.60	14.58	15.20	16.00
19	14.40	15.38	16.00	16.80
20	15.20	16.18	16.80	17.60
21	16.00	16.98	17.60	18.40
22	16.80	17.78	18.40	19.20
23	17.60	18.58	19.20	20.00
24	18.40	19.38	20.00	20.80



A型



B型

TOLERANCE UNLESS OTHERWISE	
X.	±0.30 X° ±5°
.X	±0.20 .X° ±2°
.XX	±0.08 .XX° ±1°
.XXX	±0.03 .XXX° ±0.5°

DRAWN	CK tan
CHKD	
APPD	
VIEW	

XFCN 兴飞连接器有限公司
 XFCN CONNECTORS CO.,LTD.
 PRODUCT NAME: 0.80mm IDC Style Connectors
 PART. NO.: M0800HI-xx-GN

SHEET	1/1
DATE	2020. 04. 12
UNITS	mm
SCALE	1:1
DWG. NO.	009

AO	MODIFICATION	DRAW	DATE
VER			