

OL17 Series




Detailed introduction:




Material and spec:

Coupling	Threaded Coupling
Shell Material	Nylon66, Fire Resistance: V-0
Insert Material	PPS Max Temperature 260°C
Contact Material	Brass With Gold Plating
Termination	Solder
Cable Outer Diameter Range	7-10mm
IP Class	P67/IP68
Mating Cycle	>500
Temperature Range	-25°C~+85°C
Insulation Resistance	2000M Ω

Product structure:



Product specifications:



Contact arrangement and spec:

Number of contact	2	3	4	5	7	9
Male contact face view						
Rated current(A)	15A	10A	5A	5A	5A	5A
Contact diameter	Φ1.5x2	Φ1.5x3	Φ1x4	Φ1x5	Φ1x7	Φ1x9
Rated voltage(AC.V)	500V	500V	500V	500V	400V	400V
Test voltage(AC.V)1min	1500V	1500V	1500V	1500V	1200V	1200V