

Product Ming	Duke FB1 decibel meter
Measuring range	30~130dBA
accuracy	±1.5dB
frequency response	31.5Hz~8KHz
Frequency-weighted characteristics	A-weighted
resolution (of image, monitor etc)	0.1dB
Working temperature and humidity	0~40°C, 10~80%RH
Storage temperature and humidity	-10~60°C, 0~90%RH
power supply	3*1.5V AAA batteries
weight	80.08g (without battery)
external dimension	50*30*159.5mm