3M[™] Wiremount Plug

.100" × .100" Connector for .050" Pitch Cable

4600 Series



- Shrouded to protect against physical and chemical pin damage
- Open or closed end covers available
- Optional ejector latches
- Accepts flat cable or discrete wire
- Military (with 3518 polarizing key) and centerbump polarization available
- Optional mounting flanges
- · Optional metal strain relief
- RoHS Compliant. See the Regulatory Information Appendix (RIA) in the "RoHS Compliance" section of www.3Mconnectors.com for compliance information (RIA E1 & C1 apply)

Date Modified: March 21, 2012

TS-0086-C Sheet 1 of 4

Physical

Insulator:

Material: Glass Filled Polyester (PBT)

Flammability: UL 94V-0

Color: Gray

Contact:

Material: Copper Alloy

Plating:

Underplating and U-Slot: 100 μ" [2.54 μm] Nickel

Wiping Area: $30 \mu'' [0.76 \mu m]$ Gold

Wire Accommodation: 26 and 28 AWG Solid and Stranded

Marking: 3M Logo, Part Identification Number, and Contact Position Numbers

Electrical

Current Rating: 1A


Insulation Resistance: $> 1 \times 10^9 \,\Omega$ at $500 \,V_{DC}$ **Withstanding Voltage:** $1,000 \,V_{RMS}$ at Sea Level

Environmental

Temperature Rating: -55°C to +105°C

UL File No.: E68080


 $.100" \times .100"$ Connector for .050" Pitch Cable



$.100" \times .100"$ Connector for .050" Pitch Cable


Table 1								
Pin Qty		Polarizing						
	Α	A'	В	С	D	Е	Notches Provided	
10	1.50 [38.1]	0.90 [22.9]	0.71 [18.0]	1.20 [30.5]	0.77 [19.6]	0.85[21.6]	B or C (See Note 1)	
14	1.70 [43.2]	1.10[27.9]	0.91 [23.1]	1.40 [35.6]	0.97 [24.6]	1.05 [26.7]	ВС	
16	1.80 [45.7]	1.20 [30.5]	1.01 [25.7]	1.50 [38.1]	1.07 [27.2]	1.15 [29.2]	ABC	
20	2.00 [50.8]	1.40 [35.6]	1.21 [30.7]	1.70 [43.2]	1.27 [32.3]	1.35 [34.3]	ABC	
24	2.20 [55.9]	1.60 [40.6]	1.41 [35.8]	1.90 [48.3]	1.47 [37.3]	1.55 [41.9]	ABC	
26	2.30 [58.4]	1.70 [43.2]	1.51 [38.4]	2.00 [50.8]	1.57 [39.9]	1.65 [46.9]	ABC	
30	2.50 [63.5]	1.90 [48.3]	1.71 [43.4]	2.20 [55.9]	1.77 [45.0]	1.85 [47.1]	ABC	
34	2.70 [68.6]	2.10 [53.3]	1.91 [48.5]	2.40 [61.0]	1.97 [50.0]	2.05 [52.1]	ABC	
36	2.80 [71.1]	2.20 [55.9]	2.01 [51.1]	2.50 [63.5]	2.07 [52.6]	2.15 [54.6]	ABC	
40	3.00 [76.2]	2.40 [61.0]	2.21 [56.1]	2.70 [68.6]	2.27 [57.7]	2.35 [59.7]	ABC	
50	3.50 [88.9]	2.90 [73.7]	2.71 [68.8]	3.20[81.3]	2.77 [70.4]	2.85 [72.4]	ABC	
60	4.00 [101.6]	3.40 [86.4]	3.21 [81.5]	3.70 [94.0]	3.27 [83.1]	3.35 [85.1]	ABC	
64	4.20 [106.7]	3.60 [91.4]	3.41 [86.6]	3.90 [99.1]	3.47 [88.1]	3.55 [90.2]	ABC	

Table 2									
Ejector/Latch	Part	Dimensions							
Option	Number	F	G	Н	I				
Short	3505-16	.335 [8.51]	.726 [18.44]	0.92 [23.4]	.41 [10.4]				
Long	3505-17	.484 [12.29]	.875 [22.23]	1.07 [27.2]	.56 [14.2]				
Universal	3505-21	.484 [12.29]	.809 [20.55]	1.01 [25.65]	.56 [14.2]				



$.100" \times .100"$ Connector for .050" Pitch Cable

Table 3						
Contact Quantity	3M Part Number Series	Dimension A	Dimension B			
10	4610	1.200 [30.48]	0.945 [24.00]			
14	4614	1.400 [35.56]	1.145 [29.08]			
16	4616	1.500 [38.10]	1.245 [31.62]			
20	4620	1.700 [43.18]	1.445 [36.70]			
24	4624	1.900 [48.26]	1.645 [41.78]			
26	4626	2.000 [50.80]	1.745 [44.32]			
30	4630	2.200 [55.88]	1.945 [49.40]			
34	4634	2.400 [60.96]	2.145 [54.48]			
36	4636	2.500 [63.50]	2.245 [57.02]			
40	4640	2.700 [68.58]	2.445 [62.10]			
50	4650	3.200 [81.28]	2.945 [74.80]			
60	4660	3.700 [93.98]	3.445 [87.50]			
64	4664	3.900 [99.06]	3.645 [92.58]			
	•	_	.400 Min			



Rear Mount Panel Cutout

Notes:

- 1. Accepts #4 pan head machine screw.
- 2. For a rear mount plug connector with Ejector/Latches the recommended maximum panel thickness is .125 [3.18].
- 3. Without polarizing tabs .340 [8.64].

TS-0086-C Sheet 4 of 4

3M is a trademark of 3M Company. **Important Notice** All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M. Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M Electronics Solutions Division 6801 River Place Blvd. Austin, TX 78726-9000 U.S.A. 1-800-225-5373

www. 3 M connectors. com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

<u>3448-4614</u> <u>3448-4640</u> <u>3448-4660</u> <u>3448-4624</u> <u>3448-4620</u> <u>3448-4626</u> <u>3448-4616</u> <u>3448-4610</u> <u>3448-4650</u> <u>3448-4650</u> <u>3448-4634</u>