

**EURONORD AB 121207**



Sample photo

**Order symbol:** AB 121207  
**Product nbr:** 7083660  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074036872  
**EI. number:**  
 Finland: 3423483  
 Electric No. 8212003428  
 Denmark:  
 Electric No. Sweden: 7083660

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		122	120	65	Ingress Protection (EN 60529): IP66/IP67
inch:		4.8	4.7	2.6	Impact Resistance (EN 62262): IK07
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		ABS			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>		RAL 7035 -light grey			Flammability Rating: UL 94 HB
<b>Cover screws material:</b>		Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 650
<b>Cover colour:</b>		RAL 7035 -light grey			NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Gasket material:</b>		Polyurethane			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Temperature °C (short term):</b>		-40 ... 80 °C			SGS Fimko
<b>Temperature °C (continuous):</b>		-40 ... 60 °C			
<b>Temperature °F (short term):</b>		-40 ... 175 °F			
<b>Temperature °F (continuous):</b>		-40 ... 140 °F			

