









NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- FRAME: STEEL; NICKEL PLATED
- FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
- RIVETED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
- CONNECTOR IS PART MARKED: **DSS4XPXXB01X CONEC ABC**

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)				
							material: SEE NOTES				
							title: D-SUB MALE 37pos. CRIMP STYLE with frame and float mount				
DO NOT ALTER CAD DRAWING BY HAND					date	name		dwg no: 16K1A1100 part no: DSS4XPXXB01X		DIN-A3 sh: 1	
					drawn 16.02.04	Lehmenkühler					
					appd. 16.02.04	Mickenbecker					
					norm						
				d-old							
4 x b		Ä5047		17.01.2014		Lehm.					
a		Original									
rev.		description		date		name					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

DSS4XPXXB01X