


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NO. * | A ±.030 ±(.762) | B | C | WEIGHT lbs./100 (g) / pcs. |
|-----------------------|-----------------------|----------------|----------------|----------------------------------|
| MP150 | 1.50 (38.1) | 1.03 (26.2) | 1.69 (42.9) | 0.07 (30) |
| MP175 | 1.75 (44.4) | 1.28 (32.5) | 1.94 (49.3) | 0.08 (36) |
| MP200 | 2.00 (50.8) | 1.53 (38.9) | 2.19 (55.6) | 0.09 (30) |
| MP250 | 2.50 (63.5) | 2.03 (51.6) | 2.69 (68.3) | 0.12 (55) |
| MP350 | 3.50 (88.9) | 3.03 (77.7) | — | 0.16 (75) |



- NOTES:
- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
 - USE WITH ANY OF THESE TIES:
M=MINIATURE
I=INTERMEDIATE
S=STANDARD
 - PART NO. & WEIGHT SHOWN SPECIFIES INDIVIDUAL PIECES, ADD SUFFIX "-R" TO PART NO. TO SPECIFY CONTINUOUS ROLLS OF 1000 PIECES. PART NO. MP350 IS NOT AVAILABLE IN ROLLS.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G00239GM_PB_MRKRPLTE_01

PANDUIT CORP. TINLEY PARK, ILLINOIS

IDENTIFICATION MARKER PLATE

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

SCALE NONE

DRAWING NO. G00239GM

DWG SIZE A

MAT'L: WHITE NYLON

DRWN BY JAD DATE 1/10/2000

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|----------|-----|-----|------------------------------------------------------------|----------|---|------|-----|
| 2 | 10-22-01 | LGG | | TOOK OF +/- REF FROM 'B' & 'C' DUE TO ADDED 'REF' ON REV 2 | G80239GM | 2 | | |
| 1 | 8/14/01 | LGG | | ADDED REF & UPDATED | G80239GM | 1 | | |
| R | 1-10-00 | JAD | | INITIAL RELEASE, REPLACES SS-4551 REV 5 | G80239GM | R | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[MP250-C](#) [MP250-M](#) [MP150-C](#) [MP150-M](#) [MP175-C](#) [MP175-M](#) [MP200-C](#) [MP200-M](#) [MP350-C](#) [MP350-M](#) [MP150-R](#) [MP175-R](#) [MP200-R](#) [MP250-R](#)