


Specification Sheet

Part Number: 151-00629



Clip can be installed by hand – no need for hardware or tools. Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 2.2" Long, Panel Thickness 0.03"–0.22", PA66HIRHSUV, Black, 3000/box

Article Number 151-00629

Type SOC7FT6

Color Black (BK)

Quantity Per box

Product Description Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

Short Description Standoff Bundling Clip, 2.2" Long, Panel Thickness 0.03"–0.22", PA66HIRHSUV, Black, 3000/box

Global Part Name

SOC7FT6-PA66HIRHSUV-BK

Length L (Imperial)

2.2

Length L (Metric)

56.0

Offset Length (Imperial)

1.22

Offset Length (Metric)

31.0

Fixation Method

Fir Tree

Height H (Imperial)

0.9

Height H (Metric)

22.5

Panel Thickness Min (Imperial)

0.03

Panel Thickness Max (Imperial)

0.22

Panel Thickness Min (Metric)

0.70

Panel Thickness Max (Metric)

5.75

Mounting Hole Diameter D (Imperial)

0.25 - 0.27

Mounting Hole Diameter D (Metric)

6.4 - 7.1 mm

Mounting Hole Diameter D Min (Imperial)

0.25

Mounting Hole Diameter D Max (Imperial)

0.27

Mounting Hole Diameter D Max (Metric) 7.1

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL 94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 3000

Package Quantity (Metric) 3000

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00629](#)